Product data sheet

Specifications



Contactor, Type L, multipole lighting, mechanically held, 30A, 8 pole, 600 V, 440/480 VAC 50/60 Hz coil, NEMA 1

8903LXG80V06

(!) To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Mechanically Held Lighting Contactor	
Range Of Product	8903LX	
Control Circuit	Separate control circuit	
Complementary	/	
Control Voltage	440 V AC 50 Hz 480 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50 Hz 170 VA 50/60 Hz	

	170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	8P 8 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Other Options	None	
Electrical Connection	Screw-clamp terminals	
Height	12.68 in (322 mm)	
Depth	6.02 in (153 mm)	
Width	7.80 in (198 mm)	

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	МХ	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	7.50 in (19.05 cm)	
Package 1 Width	8.00 in (20.32 cm)	
Package 1 Length	13.50 in (34.29 cm)	
Package 1 Weight	13.71 lb(US) (6.218 kg)	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov