





Contactor, Type L, multipole lighting, mechanically held, 30A, 8 pole, 600 V, 208 VAC 60 Hz coil, NEMA 4/4X

8903LXWW80V08

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	208 V AC 60 Hz	
Inrush Power In Va	180 VA 60 Hz 170 VA 50/60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	8P 8 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Other Options	None	
Electrical Connection	Screw-clamp terminals	
Height	13.90 in (353 mm)	
Depth	7.05 in (179 mm)	
Width	8.50 in (216 mm)	

Environment

Enclosure Type	NEMA 4/4X glass polyester surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)	
Discount Schedule	CP1	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	13.90 in (35.3 cm)
Package 1 Width	8.50 in (21.6 cm)
Package 1 Length	7.05 in (17.9 cm)
Package 1 Weight	83.51 lb(US) (37.88 ka)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov