

# Product data sheet

Specifications

SQUARE D



Contactor, Definite Purpose, 50A, 3 pole, 30 HP at 575 VAC, 3 phase, 208/240 VAC 60 Hz 220 VAC 50 Hz coil, open

8910DPA53V09Y125Y236

! Discontinued

! Discontinued on: Nov 11, 2020

! End-of-service on: Dec 31, 2020

## Main

Product Or Component Type	Definite Purpose Contactor
Line Rated Current	50 A
Number Of Poles	3P
Pole Contact Composition	3 NO
Range Of Product	DPA

## Complementary

Maximum Horse Power Rating	3 hp 115 V AC, 1 phase 10 hp 230 V AC, 1 phase 15 hp 230 V AC, 3 phase 30 hp 460 V AC, 3 phase 30 hp 575 V AC, 3 phase
Locked Rotor Rated Current	300 A 277 V AC 250 A 460 V AC 200 A 575 V AC
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	208...240 V AC 60 Hz 220 V AC 50 Hz
Phase	3 phase
Electrical Connection	Screw terminals Box lugs

## Environment

Product Certifications	UL Recognized CSA
------------------------	----------------------

## Ordering and shipping details

Category	21345-8910 DPA 5_(50 AMP)
Discount Schedule	CP1B
Returnability	No
Country Of Origin	CN

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Mercury Free	
<hr/>		
	Rohs Exemption Information	<a href="#">Yes</a>
<hr/>		
Eu Rohs Directive		Compliant
		<a href="#">EU RoHS Declaration</a>
<hr/>		
China Rohs Regulation		<a href="#">China RoHS declaration</a>
		Product out of China RoHS scope. Substance declaration for your information.
<hr/>		