





Pilot light, Harmony 9001K, metal, polycarbonate, fresnel, amber, 30mm, 24-28V

9001KP35A31

Product availability: Stock - Normally stocked in distribution facility

Price\*: 125.00 USD

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Pilot light
Device Short Name	K

### Complementary

Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Lens Type	Fresnel plastic
Cap/Operator Or Lens Colour	Amber
Light Source	incandescent
Bulb Base	BA 9s
Light Block Supply	Full voltage 28 V Direct 24 V
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² IEC 60947-1
Shape Of Screw Head	Round
Operating Position	Any position
Light Source	Incandescent bulb
[Us] Rated Supply Voltage	2428 V AC/DC
Operating Mode	Normal
Device Presentation	Complete product
Lens Type	Fresnel
[Us] Rated Supply Voltage	2428 V
Light Block Supply	Full voltage
Lens Material	Polycarbonate
Size	30 mm

#### **Environment**

Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR25490 class 3211 03
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901032212
Returnability	Yes
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	5.12 oz (145.15 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov