# Product data sheet

Specifications





## Head for pilot light, Harmony 9001K, metal, without cap, 30mm, 120V

9001KP38

Product availability: Stock - Normally stocked in distribution facility

### Price\*: 116.00 USD

## Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Head for pilot light	
Device Short Name	ĸ	

## Complementary

oompicinentary	
Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Cap/Operator Or Lens Colour	Without cap
Bulb Base	BA 9s
Light Block Supply	Full voltage 120 V
Shape Of Screw Head	Round
Light Source	Incandescent bulb
Operating Mode	Normal
[Us] Rated Supply Voltage	120 V
Light Block Supply	Full voltage or resistor
Size	30 mm

## Environment

Product Certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901008750
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	4.80 oz (136.078 g)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov