## Product data sheet

Specifications



# Pilot light, Harmony 9001K, metal, polycarbonate, fresnel, red, 30mm, 110-120V flashing

9001KPF1R31

() Discontinued on: Jun 30, 2023

(!) Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Pilot light
Device Short Name	К

### Complementary

Bezel Material	Metal	
Mounting Diameter	1.18 in (30 mm)	
Lens Type	Fresnel plastic	
Cap/Operator Or Lens Colour	Red	
Bulb Base	BA 9s	
Light Block Supply	Direct 110 V AC 50/60 Hz Direct 120 V AC 50/60 Hz	
Shape Of Screw Head	Round	
Light Source	Incandescent bulb	
Operating Mode	Normal	
Lens Type	Fresnel	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Flashing	
Supply Frequency	5060 Hz	
Lens Material	Polycarbonate	
Size	30 mm	

### Environment

Product Certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

## Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901033257

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	8.00 oz (226.796 g)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	