Product data sheet

Specifications





Push button, Harmony 9001K, metal, mushroom 35mm, red, 30mm, spring return, 1 NC

9001KR24RH6

Product availability: Stock - Normally stocked in distribution facility

Price*: 112.00 USD

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Push-button	
Device Short Name	К	
Type Of Operator	spring return	
Operator Profile	Red mushroom Ø 35 mm	
Operator Additional Information	Screw-on plastic with set screw	

Complementary

· · · · · · · · · · · · · · · · · ·	
Bezel Material	Metal
Mounting Diameter	1.18 in (30 mm)
Light Source	without
Light Source	Without
Light Block Supply	Without supply
Contacts Type And Composition	1 NC
Connections - Terminals	Screw clamp terminals
Operating Position	Any position
[le] Rated Operational Current	10 A, AC-15 10 A, DC-13
Contact Operation	Standard
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Red
Operator Profile	Mushroom Ø 35 mm
Type Of Operator	Spring return
Size	30 mm

Environment

Product Certifications	NEMA UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901033516
Returnability	Yes
Country Of Origin	МХ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	5.12 oz (145.15 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov