

Product data sheet

Specifications



Key-operated pushbutton head, Harmony 9001K, metal, key switch, 30mm, key E10, flush position, stay put

9001KR133

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 132.50 USD

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for key-operated pushbutton
Device Short Name	9001K
Operator Profile	flush

Complementary

Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Key Number	E10
Bezel Material	Metal
Operator Profile	Key switch
Type Of Operator	Stay put
Operator Position Information	Flush position
Contacts Type And Composition	Without contact block

Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901260516
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	6.24 oz (176.901 g)
------------------	---------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov