Product data sheet

Specifications



Push-button, Harmony 9001K, metal, flush, black, 30mm, spring return, 2 NO

9001KR1BH7

() Discontinued on: Jun 30, 2023

(!) Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-button
Device Short Name	К
Operator Profile	Black flush
Operator Additional Information	Metal guard

Complementary

Bezel Material Metal Mounting Diameter 1.18 in (30 mm) Light Source Without Light Block Supply Without supply Contacts Type And Composition 2 NO [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return Size 30 mm	· · · · · · · · · · · · · · · · · · ·		
Light Source Without Light Block Supply Without supply Contacts Type And Composition 2 NO [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	Bezel Material	Metal	
Light Block Supply Without supply Contacts Type And Composition 2 NO [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	Mounting Diameter	1.18 in (30 mm)	
Contacts Type And Composition 2 NO [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	Light Source	Without	
[le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	Light Block Supply	Without supply	
10 A, DC-13 Contact Operation Standard Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	Contacts Type And Composition	2 NO	
Device Presentation Complete product Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	[le] Rated Operational Current		
Cap/Operator Or Lens Colour Black Operator Profile Flush Type Of Operator Spring return	Contact Operation	Standard	
Operator Profile Flush Type Of Operator Spring return	Device Presentation	Complete product	
Type Of Operator Spring return	Cap/Operator Or Lens Colour	Black	
	Operator Profile	Flush	
Size 30 mm	Type Of Operator	Spring return	
	Size	30 mm	

Environment

Product Certifications	CE CSA LR 25490 class 3211 03 NEMA UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	785901033318	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.43 in (29.032 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	29.03 in (73.742 cm)
Package 1 Weight	8.00 oz (226.796 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov