Product data sheet

Specifications



PUSH BUTTON 600VAC 10A 30MM T-K

9001KR1UH4

() Discontinued on: May 6, 2021

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Bezel Material	Chromium plated metal
Control Button Type	standard push-button
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Light Source	without
Mounting Diameter	1.18 in (30 mm)
Operator Additional Information	Full quard in metal

Complementary

Line Rated Current	10 A	
Cap/Operator Or Lens Colour	1 black	
	1 blue	
	1 white	
	1 green	
	1 red	
	1 orange	
	1 yellow	
Contact Operation	Standard fingersafe	
Contacts Type And Composition	4 NO + 4 NC	
Control Type	push-button	
Electrical Connection	Screw clamp terminal	
Light Block Supply	Without supply	
	Without supply	
Marking	unmarked	
Mounting Support	panel	
Operator Position Information	2 positions	
Operator Profile	1 projecting push-button	
Permissible Voltage	600 V	
Shape	Round head	
Type Of Operator	Momentary	
Utilisation Category	AC-15	
	DC-13	

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	00785901847618	
Returnability	No	
Country Of Origin	МХ	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov