Product data sheet

Specifications



① Discontinued

PUSH BUTTON 600VAC 10A 30MM T-K

9001KR3BH6

() Discontinued on: Dec 2, 2020

(!) End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony 9001K |
|---------------------------------|------------------|
| Product Or Component Type | Push-button |
| Device Short Name | К |
| Type Of Operator | spring return |
| Operator Profile | Black projecting |
| Operator Additional Information | Without guard |

Complementary

| · · · · · · · · · · · · · · · · · · · | |
|---------------------------------------|----------------------------|
| Bezel Material | Chromium plated metal |
| Mounting Diameter | 1.18 in (30 mm) |
| Light Source | without |
| Light Source | Without |
| Light Block Supply | Without supply |
| Contacts Type And Composition | 1 NC |
| Connections - Terminals | Screw clamp terminals |
| Operating Position | Any position |
| [Ie] Rated Operational Current | 10 A, AC-15 10 A, DC-13 |
| Contact Operation | Standard |
| Device Presentation | Complete product |

Environment

| Product Certifications | CE NEMA UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 |
|---------------------------|--|
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| Category | US10CS121426 | |
|-------------------|----------------|--|
| Discount Schedule | 0CS1 | |
| Gtin | 00785901033738 | |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Returnability | No |
|-------------------|----|
| Country Of Origin | MX |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |