# Product data sheet

Specifications





## SELECTOR SWITCH OPERATOR 30MM T-K

9001KS53K5E46

- () Discontinued on: Dec 2, 2020
- (!) End-of-service on: Dec 31, 2020



#### Main

Range Of Product	Harmony 9001KS	
Product Or Component Type	Selector switch	
Device Short Name	9001KS	
Type Of Operator	Both sides to centre spring return	
Operator Profile	Black key switch	

#### Complementary

Chromium plated metal
1.18 in (30 mm)
0.54 lb(US) (0.245 kg)
Round
3 positions
E46
Center
Without contact block
500000 cycles
Basic element

### Environment

Protective Treatment	тс	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Overvoltage Category	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 4 NEMA 6	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Standards	EN/IEC 60947-1 UL 508 JIS C 4520 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-1 EN/IEC 60947-5-4	
Product Certifications	UL 508 NEMA	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	

# Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov