Product data sheet

Specifications

SQUARE D



selector switch Ø 30 - 3 positions - maintained - incandescent

9001SK42J1G

() Discontinued on: Jan 23, 2021



Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Selector switch
Device Short Name	9001SK
Type Of Operator	maintained
Operator Profile	Green standard knob

Complementary

Complementary		
Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Net Weight	0.13 lb(US) (0.059 kg)	
Shape Of Signaling Unit Head	Round	
Operator Position Information	3 positions	
Contacts Type And Composition	Without contact block	
Mechanical Durability	500000 cycles	
Light Block Supply	Via integral transformer	
Light Source	incandescent	
Bulb Base	BA 9s	
[Us] Rated Supply Voltage	110120 V AC 50/60 Hz	
Compatibility Code	9001SK	

Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
	NEMA 6
Standards	JIS C 4520 UL 508 JIS C 852 EN/IEC 60947-5-1 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-1
Product Certifications	NEMA UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Gtin	00785901287674
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov