





Selector switch head, Harmony 9001K, metal, standard handle, black, 30mm, 3 positions, return both sides to center

9001KS501B

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 81.00 USD

### Main

Product Or Component Type	Head for selector switch
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)
Range Of Product	Harmony 9001K

### Complementary

Bezel Material	Metal
Cap/Operator Or Lens Colour	black
Contacts Type And Composition	Without contact block
Operator Position Information	3 positions
Operator Profile	Standard handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Spring return both sides to centre
Cap/Operator Or Lens Colour	Black
Type Of Operator	Spring return
Contacts Type And Composition	Without contact block

### **Environment**

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901820727
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)
Package 1 Weight	4.32 oz (122.47 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations