





Timing Relay, Type JCK, plug In, on delay, adjustable time, 1.2 to 120 seconds, 10A, 240 VAC, 24 VAC/DC

9050JCK14V14

① Discontinued

! Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Range	9050JCK
Product Type	Timer
Timing Mode	On-delay
Timing Range	1.2120 s
Supply Voltage	24 V AC/DC

Complementary

Power Consumption	2 VA	
Current Rating	10 A	
Switch Function	DPDT	
Contact Composition	2 NO + 2 NC	
Contact Material	Silver nickel	
Maximum Switching Voltage	240 V AC	
Mounting Type	Socket	
Number Of Pins	8	
Shape Of Pins	s Tubular	
For Use With	8501NR51 8501NR52	

Environment

Certifications	CE UL Recognized UL Listed
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category US10CP221651

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2	
Gtin	785901056362	
Returnability	No	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.40 in (11.176 cm)
Package 1 Width	2.70 in (6.858 cm)
Package 1 Length	2.00 in (5.08 cm)
Package 1 Weight	5.28 oz (149.686 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information