Product data sheet

Specifications







Selector switch head, Harmony 9001SK, plastic, without handle, 30mm, 2 positions, spring return right to left

9001SKS34

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 106.50 USD

Main

Product Or Component Type	Head for selector switch
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)
Range Of Product	Harmony 9001SK

Complementary

Bezel Material	Plastic
Cap/Operator Or Lens Colour	without cap
Contacts Type And Composition	Without contact block
Operator Position Information	2 positions
Operator Profile	Without handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Spring return right to left
Type Of Operator	Spring return
Contacts Type And Composition	Without contact block

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CE CSA LR24590 class 3211 03

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901017530
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)
Package 1 Weight	3.20 oz (90.719 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov