Product data sheet

Specifications







Transformer, Type T, industrial control, 150VA, 1 phase, 240/480/600V primary, 120V secondary, 55C rise

9070T150D32

Product availability: Stock - Normally stocked in distribution facility

Price*: 328.00 USD

Main

Product Type	Industrial Control Transformer
Туре	т

Complementary

Number Of Phases	1 phase
Power Rating	150 VA UL
	150 VA CSA
	150 VA NOM
	150 VA CE
Primary To Secondary Voltage	240/480/600 V 100/120 V
	230/460/575 V 95/115 V
	220/440/550 V 90/110 V
Temperature Rise	55 °C
Electrical Connection	Screw clamp terminals
Height	3.2 in (81.28 mm)
Width	3.75 in (95.25 mm)
Depth	3.59 in (91.19 mm)
Material	Copper: winding
Fingersafe Cover Compatibility	FSC1

Environment

Certifications	UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation Temperature	221 °F (105 °C)

Ordering and shipping details

Category	US10CP816206
Discount Schedule	0CP8
Gtin	785901845621
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.63 in (14.3 cm)
Package 1 Width	6.42 in (16.3 cm)
Package 1 Length	7.01 in (17.8 cm)
Package 1 Weight	5.94 lb(US) (2.694 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	150
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	36.02 in (91.5 cm)
Package 2 Length	48.03 in (122.0 cm)
Package 2 Weight	885.82 lb(US) (401.8 kg)

Contractual warranty

Warranty

10 Years

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov