





Transformer, EO, industrial control, 300VA, 1 phase, 240x480V primary, 120V secondary, 80C rise

9070EO4D1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 601.00 USD

### Main

Product Or Component Type	Industrial Control Transformer
Range Of Product	EO

### **Complementary**

•	,
Phase	1 phase
Rated Power In Va	300 VA
Primary Voltage	240 x 480 V 230 x 460 V
	220 x 440 V
Secondary Voltage	120 V 115 V
Temperature Rise	110 V
Temperature Rise	80 °C
Electrical Connection	Screw clamp terminals
Height	5.55 in (141 mm)
Width	4.49 in (114 mm)
Depth	3.74 in (95 mm)
Net Weight	17.20 lb(US) (7.8 kg)

### **Environment**

Product Certifications	CE CSA UL Listed
Nema Degree Of Protection	Not rated (open device)
Insulation Temperature	266 °F (130 °C)

### Ordering and shipping details

Category	US10CP816208	
Discount Schedule	0CP8	
Gtin	785901837831	
Returnability	Yes	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.40 in (16.256 cm)
Package 1 Width	6.90 in (17.526 cm)
Package 1 Length	7.80 in (19.812 cm)
Package 1 Weight	10.50 lb(US) (4.763 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov