





Transformer, Type T, industrial control, 300VA, 1 phase, 240x480V primary, 120V secondary, 80C rise

9070T300D1

Product availability: Stock - Normally stocked in distribution facility

Price*: 383.00 USD

Main

Product Type	Industrial Control Transformer
Туре	Т

Complementary

Number Of Phases	1 phase	
Power Rating	300 VA UL	
	300 VA CSA	
	300 VA NOM	
	200 VA CE	
Primary To Secondary Voltage	240 x 480 V 120 V	
	230 x 460 V 115 V	
	220 x 440 V 110 V	
Temperature Rise	80 °C	
Electrical Connection	Screw clamp terminals	
Height	3.84 in (97.54 mm)	
Width	4.5 in (114.30 mm)	
Depth	4.74 in (120.40 mm)	
Material	Copper: winding	
Fingersafe Cover Compatibility	FSC2	

Environment

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	266 °F (130 °C)

Ordering and shipping details

Category	US10CP816201	
Discount Schedule	0CP8	
Gtin	785901904687	
Returnability	Yes	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.90 in (9.906 cm)
Package 1 Width	4.74 in (12.04 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	9.38 lb(US) (4.255 kg)

Contractual warranty

Warranty 10 Years



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov