


# Product data sheet

Specifications

SQUARE D



Terminal block, Linergy, transient voltage suppressor, natural colored block, 120 VAC

9080GT6

Product availability: Stock - Normally stocked in distribution facility

! Discontinued

## Main

Range Of Product	9080G
Product Type	Terminal block
Localisation On Device	Transient voltage suppressor
Color	Natural
Quantity	Set of 5

## Complementary

Voltage Rating	120 V AC
Wire Size	AWG 18...AWG 10 copper
Mounting Type	9080GH track 35 mm DIN rail
Certifications	UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01 CE
Protection Type	Fingersafe DIN 57470
Electrical Connection	Copper box lugs
Material	Nylon: block
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug copper 18...20 lbf.in (2.03...2.26 N.m) : AWG 18...AWG 10 copper)
Height	2.55 in (64.77 mm)
Width	2.16 in (54.86 mm)
Depth	0.5 in (12.70 mm)
Density	24 per foot
Compatible End Barrier	GT6B

## Ordering and shipping details

Category	US10CP521702
Discount Schedule	0CP5
Gtin	785901652441
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability






**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
 Pvc Free	
<b>Reach Regulation</b>	<a href="#">REACH Declaration</a>
<b>Eu Rohs Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
<b>California Proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a>