Product data sheet

Specifications



Transformer, Type T, industrial control, 5000VA, 1 phase, 600V primary, 120V secondary, 115C

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Type	Industrial Control Transformer
Туре	Т

Complementary

Number Of Phases	1 phase	
Power Rating	5000 VA UL	
	5000 VA CSA	
	5000 VA NOM	
	3000 VA CE	
Primary To Secondary Voltage	600 V 120 V	
	575 V 115 V	
	550 V 110 V	
Temperature Rise	115 °C	
Electrical Connection	Screw clamp terminals	
Height	8.75 in (222.25 mm)	
Width	9 in (228.60 mm)	
Depth	9.15 in (232.41 mm)	
Material	Copper: winding	
Fingersafe Cover Compatibility	FSC2	

Environment

Certifications	CSA file LR37055 guide 184-N-90 UL listed file E61239
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

Ordering and shipping details

Category	US10CP816205
Discount Schedule	0CP8
Gtin	785901508755
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.50 in (31.75 cm)
Package 1 Width	12.38 in (31.445 cm)
Package 1 Length	12.38 in (31.445 cm)
Package 1 Weight	90.80 lb(US) (41.186 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov