## Product data sheet

Specifications

#### SQUARE D





# Safety switch, double throw, non fusible, 30A, 240V, 2 pole, NEMA 1, fuse class T4

92251

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 585.00 USD

#### Main

Product	Double Throw Safety Switch		
Duty Rating	General duty		
Disconnect Type	Non-fusible disconnect		
Factory Installed Neutral	None		
Number Of Poles	2		
Current Rating	30 A		
Voltage Rating	240 V AC		
Enclosure Rating	NEMA 1		

#### Complementary

Short-Circuit Current	10 kA H or K H or K		
Fuse Type			
Mounting Type	Surface		
Wire Size	AWG 12AWG 2 aluminium AWG 14AWG 2 copper		
Tightening Torque	35 lbf.in (3.95 N.m) 0.000.01 in <sup>2</sup> (2.085.26 mm <sup>2</sup> ) (AWG 14AWG 10) 40 lbf.in (4.52 N.m) 0.01 in <sup>2</sup> (8.37 mm <sup>2</sup> ) (AWG 8) 45 lbf.in (5.08 N.m) 0.020.03 in <sup>2</sup> (13.321.15 mm <sup>2</sup> ) (AWG 6AWG 4) 50 lbf.in (5.65 N.m) 0.040.05 in <sup>2</sup> (26.6733.62 mm <sup>2</sup> ) (AWG 3AWG 2)		
Depth	4.75 in (120.65 mm)		
Width	9.75 in (247.65 mm)		
Height	10 in (254.00 mm)		
Net Weight	7.58 lb(US) (3.44 kg)		

#### Environment

Certifications

UL Listed

### Ordering and shipping details

Category	US10DE100033
Discount Schedule	0DE1
Gtin	785901454465
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country	Of	Origin	
---------	----	--------	--

#### **Packing Units**

J			
Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	5.30 in (13.462 cm)		
Package 1 Width	10.00 in (25.4 cm)		
Package 1 Length	11.00 in (27.94 cm)		
Package 1 Weight	7.65 lb(US) (3.47 kg)		

#### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

REACh Declaration			
Compliant			
EU RoHS Declaration			
China RoHS declaration			
Pro-active China RoHS declaration (out of China RoHS legal scope)			
Product Environmental Profile			
No need of specific recycling operations			
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			