

Product data sheet

Specifications



Terminal block, Linergy TR, clip on mounting, splitter block

AB3RV162U

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 78.00 USD

Complementary

Line Rated Current	150 A 1P busbar
Electrical Connection	1 solid upstream 0.05 in² (35 mm²) connector 1 flexible upstream 0.04 in² (25 mm²) connector 6 solid downstream 0.00...0.01 in² (0.5...6 mm²) tap-off 6 flexible downstream 0.00...0.01 in² (0.5...4 mm²) tap-off
Fixing Mode	Clip-on
Mounting Support	rail
Product Compatibility	Universal fixing frames
Product Destination	terminal block

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
Gtin	3389110588002
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.31 in (13.500 cm)
Package 1 Width	5.00 in (12.700 cm)
Package 1 Length	6.10 in (15.500 cm)
Package 1 Weight	3.21 oz (91.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	5.31 in (13.500 cm)
Package 2 Width	5.00 in (12.700 cm)
Package 2 Length	6.10 in (15.500 cm)
Package 2 Weight	32.35 oz (917.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	40
Package 3 Height	5.91 in (15 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	8.75 lb(US) (3.970 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

<div>✓</div>	Reach Free Of Svhc	
<div>✓</div>	Toxic Heavy Metal Free	
<div>✓</div>	Mercury Free	
<div>✓</div>	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	