



# Product data sheet

Specifications



## InRow RD, 600mm, Air Cooled, 200-240V, 50/60Hz

ACRD500

-  **Discontinued on:** Apr 1, 2016
-  **To be end-of-service on:** Mar 31, 2026

 **Discontinued - Service only**

### Overview

Lead Time	Special Order - Call for Quoted Lead Times
-----------	--

### Main

Main Input Voltage	200 V 3 phase 208 V 3 phase 220 V 3 phase 240 V 3 phase
Number Of Rack Unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

### General

Compressor Type	Reciprocating
Air Flow	4600 ft³/min (2170.96 l/s)
Condensate Pump Capacity	8.45 Gal/hr(US) (0.03 m3/h)

### Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	809.69 lb(US) (367.27 kg)
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

### Input

Input Frequency	50/60 Hz
Number Of Input Connectors	1 Hard Wire 4-wire (3PH + G)

### Conformance

Product Certifications	cUL Listed CE Industry Canada UL Listed VDE
------------------------	---

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Communications & Management

Control Panel	Multi-function LCD status and control console
---------------	---

## Ordering and shipping details

Gtin	731304262565
------	--------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	85.28 in (216.6 cm)
Package 1 Width	44.76 in (113.7 cm)
Package 1 Length	33.46 in (85 cm)
Package 1 Weight	947.00 lb(US) (429.55 kg)

## Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up
----------	--

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

**Eu Rohs Directive**

Not applicable, out of EU RoHS legal scope

---