# Product data sheet

Specifications





# Plug outlet, Linergy HK, 3P, 16A, 2 points, 2.5mm<sup>2</sup>, cable length 200

AK5PC13

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 15.60 USD

#### Main

Range	Linergy
Product Name	НК
Product Or Component Type	Plug outlet
Poles Description	3P
[Ith] Conventional Free Air Thermal Current	16 A
I <sup>2</sup> T On Activation	100000 A².s
Number Of Points	2
Number Of Cables	3 0.00 in² (2.5 mm²)
Cable Length	0.66 ft (0.2 m)
Quantity Per Set	Set of 6

### Complementary

[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
Width	1.42 in (36 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.09 lb(US) (0.04 kg)

#### **Environment**

Standards	IEC 60439
Product Certifications	DNV LROS (Lloyds register of shipping) UL CSA

## Ordering and shipping details

Category	US10I1122623
Discount Schedule	0111
Gtin	3389110576818
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.500 cm)
Package 1 Width	3.54 in (9.000 cm)
Package 1 Length	4.72 in (12.000 cm)
Package 1 Weight	1.55 oz (44.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	5.00 in (12.700 cm)
Package 2 Width	5.12 in (13.000 cm)
Package 2 Length	5.91 in (15.000 cm)
Package 2 Weight	11.46 oz (325.000 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	96
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	13.09 lb(US) (5.937 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>②</b>	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations