





Adaptor, I-Line Busway, max 1350A rated, aluminum, bolt connection, 4 wire, mounted indoors

AF2513G12B

Price\*: 3,304.00 USD

#### Main

Product	Adaptor
Range	I-Line

# Complementary

Rated Current	1350 A aluminium
Rated Operational Voltage	600 V AC/DC 50/60 Hz
Length	12 in (304.80 mm)
Material	Aluminium: busbar
I-Line Value End	Bolt
Number Of Phases	3 phase
For Use With	Busbar trunking 1350 A aluminium
Protection Type	50 percent capacity integral ground bus
Wiring Configuration	4-wire
Mounting Location	Indoor

### **Environment**

Standards	UL 857	
	CSA C22.2 No 27:1994	
	IEC 61430 6	

### Ordering and shipping details

Category	20008-AF2/AFH2 1350A 4WIRE-COMM
Discount Schedule	PE8
Gtin	785901164739
Returnability	No
Country Of Origin	US

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.88 in (14.935 cm)
Package 1 Width	7.34 in (18.644 cm)
Package 1 Length	13.00 in (33.02 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Weight

38.94 lb(US) (17.663 kg)

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

**Reach Regulation** 

Eu Rohs Directive	Compliant
Eu Rons Directive	'
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

**REACh Declaration**