



Straight length, I-Line Busway, 225A, 600VAC, 3 phase, 4 wire, integral ground bus, Al, plug-in, 10ft

AP502G10

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 5,803.56 USD

Main

Range Of Product	I-Line
Product Or Component Type	Straight length
Application	Plug-in

Complementary

Line Rated Current	225 A
Short Circuit Rating	22 kA
Busbar Material	Aluminium: busbar
Integral Ground/High Short Circuit Bracing	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number Of Phases	3 phase
Wiring Configuration	4-wire
Length	10 ft (3.05 m)

Ordering and shipping details

Category	US10PE820064
Discount Schedule	0PE8
Gtin	785901653417
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.98 in (15.2 cm)
Package 1 Width	2.24 in (5.7 cm)
Package 1 Length	120.51 in (306.1 cm)
Package 1 Weight	67.00 lb(US) (30.391 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation

Eu Rohs Directive	Compliant
Eu Rons Directive	'
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

REACh Declaration