Product data sheet

Specifications



Straight length, I-Line Busway, 3000A, 600VAC, 3 phase, 4 wire, integral ground bus, Al, feeder, 10ft

AF2530G10ST

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 34,426.60 USD

Main

Range Of Product	I-Line
Product Or Component Type	Straight length
Application	Feeder

Complementary

· · · · · · · · · · · · · · · · · · ·	
Line Rated Current	3000 A
Short Circuit Rating	100 kA
Busbar Material	Aluminium: busbar
Integral Ground/High Short Circuit Bracing	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number Of Phases	3 phase
Wiring Configuration	4-wire
Length	10 ft (3.05 m)

Environment

Product Certifications	UL listed file E22182
Standards	CSA C22.2 No 27:1997 IEC 61439-2 UL 857

Ordering and shipping details

Category	US10PE820015
Discount Schedule	0PE8
Gtin	785901060376
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	282.15 lb(US) (127.981 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov