

Product data sheet

Specifications



connecting cable, Modicon M340,
USB, PC or terminal, for processor,
1.8m

BMXXCAUSBH018

Product availability: Stock - Normally stocked in distribution facility

Main

Range Of Product	Modicon M340 automation platform Modicon M262
Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Terminal port/USB cordset
Accessory / Separate Part Designation	3.4" small touch screen panel 3.5" small touch screen panel
Accessory / Separate Part Destination	Graphic terminal XBTGT, XBTGK, XBTGTW PC terminal
Range Compatibility	Harmony GTO Modicon M262
Cable Length	5.91 ft (1.8 m)

Complementary

Electrical Connection	1 connector USB type A 1 connector mini B USB M340 processor)
Net Weight	0.14 lb(US) (0.065 kg)

Ordering and shipping details

Category	US1PC3418160
Discount Schedule	PC34
Gtin	3595863920208
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.98 in (2.5 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	6.50 in (16.5 cm)
Package 1 Weight	1.87 oz (53.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	200
Package 2 Height	11.81 in (30.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	25.02 lb(US) (11.349 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration
-----------------------	--

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--

California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
---------------------------	---