

Product data sheet

Specifications



Thermistor probe, TeSys LT3,
integrated triple probe, 170°C, 0 to
2.5V, bulk qty

DA1TT170

⚠ Discontinued on: Aug 9, 2022

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range Of Product	DA1
Product Or Component Type	Thermistor probe
Device Short Name	DA1TT
Accessory / Separate Part Category	Protection accessory
Quantity Per Set	Set of 10
Ambient Air Temperature For Operation	338 °F (170 °C)

Complementary

[Ui] Rated Insulation Voltage	2500 V
[Ue] Rated Operational Voltage	<= 2.5 V
Resistance	250 Ohm per probe 25 °C
Insulation	Reinforced
Cable Length	3.28 ft (1 m) between probe and motor terminal plate 9.84 in (250 mm) between probes
Net Weight	0.02 lb(US) (0.01 kg)

Environment

Standards	IEC 60034-11 Mark A
-----------	---------------------

Ordering and shipping details

Category	US10I1122339
Discount Schedule	0I11
Gtin	3389110531909
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	3.54 in (9.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	4.92 in (12.5 cm)
Package 1 Weight	0.32 oz (9.0 g)
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	0.59 in (1.5 cm)
Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	4.92 in (12.5 cm)
Package 2 Weight	3.28 oz (93.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	2.27 lb(US) (1.03 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov