

# Product data sheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical 8.5mm x 31.5mm, fuse type gG, 400VAC, 12A, without striker, set of 10 parts

DF2BN1200

⚠ Discontinued

## Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF2
[Ue] Rated Operational Voltage	400 V AC
Line Rated Current	12 A 400 V
Fuse Size	8.5 x 31.5 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

## Complementary

Fuse Curve	GG
Net Weight	0.02 lb(US) (0.01 kg)

## Ordering and shipping details

Category	22621-IEC PANEL ACCESSORIES
Discount Schedule	I
Gtin	3389110499421
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.47 in (1.2 cm)
Package 1 Width	0.20 in (0.5 cm)
Package 1 Length	2.76 in (7.0 cm)
Package 1 Weight	0.14 oz (4.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	0.47 in (1.2 cm)
Package 2 Width	1.77 in (4.5 cm)
Package 2 Length	2.76 in (7.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	1.59 oz (45.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	400
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	4.40 lb(US) (1.995 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov	