Specifications

SQUARE D

Green



Safety switch, double throw, non fusible, 100A, 600V, 3 pole, 100HP, NEMA 1

DTU363

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,036.00 USD

Main

Product	Double Throw Safety Switch	
Duty Rating	Heavy duty	
Disconnect Type	Non-fusible disconnect switch	
Factory Installed Neutral	stalled Neutral None	
Number Of Poles	3	
Current Rating	100 A	
Voltage Rating	600 V AC 600 V DC	
Enclosure Rating	NEMA 1	
Motor Power Hp	20 hp at 240 V AC 50-60 Hz for 1 phase motors 40 hp at 240 V AC 50-60 Hz for 3 phase motors 40 hp at 480 V AC 50-60 Hz for 1 phase motors 75 hp at 480 V AC 50-60 Hz for 3 phase motors 40 hp at 600 V AC 50-60 Hz for 1 phase motors 100 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 250 V DC 50 hp at 600 V DC	

Complementary

10 kA H or K
200 kA R, J or T
H or K
R, J or T
Surface
AWG 12AWG 1/0 aluminium
AWG 14AWG 1/0 copper
35 lbf.in (3.95 N.m) 0.000.01 in ² (2.065.26 mm ²) (AWG 14AWG 1/0)
40 lbf.in (4.52 N.m) 0.01 in ² (8.37 mm ²) (AWG 8)
45 lbf.in (5.08 N.m) 0.020.08 in ² (13.3053.48 mm ²) (AWG 8)
50 lbf.in (5.65 N.m) 0.040.08 in² (26.6753.48 mm²) (AWG 6AWG 4)
6.93 in (176.02 mm)
11.96 in (303.78 mm)
29.94 in (760.48 mm)
39.00 lb(US) (17.69 kg)

Environment

Certifications

UL Listed

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100033
Discount Schedule	0DE1
Gtin	785901308683
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.30 in (26.162 cm)
Package 1 Width	12.40 in (31.496 cm)
Package 1 Length	32.70 in (83.058 cm)
Package 1 Weight	36.26 lb(US) (16.447 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov