Product data sheet

Specifications





Cable end, Linergy TR cable ends, Single conductor, yellow, 25mm², medium size, markable, 10 sets of 100

DZ5CA002

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.26 USD

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	0.00 in² (0.25 mm²)

Complementary

Cable End Type	Single conductor
Additional Information	With integrated marker tag holder
Color	Yellow
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	1
Awg Gauge	AWG 26
Bezel Size	Ø 2.3 mm
Tube Diameter	0.04 in (1.1 mm)
Length	0.47 in (12 mm)
Tube Length	0.31 in (8 mm)
Cad Overall Depth	1.18 in (30 mm)
Net Weight	0.31 lb(US) (0.14 kg)

Environment

Ambient Air Temperature For	-4221 °F (-20105 °C)
Operation	, ,

Ordering and shipping details

Category	US1000l22621
Discount Schedule	0001

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Gtin	3389110535396
Returnability	No
Country Of Origin	DE

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.400 cm)
Package 1 Width	0.16 in (0.400 cm)
Package 1 Length	0.55 in (1.400 cm)
Package 1 Weight	0.00 oz (0.100 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	1.57 in (4.000 cm)
Package 2 Width	3.94 in (10.000 cm)
Package 2 Length	7.87 in (20.000 cm)
Package 2 Weight	4.41 oz (125.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	20000
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	6.30 lb(US) (2.856 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes
 Pvc Free
 Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations