Product data sheet

Specifications





Cable ends, Linergy TR cable ends, single conductor, green, 0.34mm², short size, 10 sets of 100

DZ5CE003L6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 0.24 USD

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Short
Standards	NF C 63-023
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	0.00 in² (0.34 mm²)

Complementary

Cable End Type	Single conductor
Additional Information	Without marker tag holder
Color	Green
Bezel Material	Halogen-free plastic
Tube Material	Copper ISO 1337
Number Of Cables	1
Awg Gauge	AWG 24
Bezel Size	Ø 2.5 mm
Tube Diameter	0.04 in (1.1 mm)
Length	0.39 in (10 mm)
Tube Length	0.24 in (6 mm)
Net Weight	0.12 lb(US) (0.055 kg)

Environment

Ambient Air Temperature For $-4...221~^{\circ}\text{F} \ (-20...105~^{\circ}\text{C})$ Operation

Ordering and shipping details

Category	US1000I22621
Discount Schedule	0001
Gtin	3389110210439

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	DF	

Packing Units

9		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.16 in (0.400 cm)	
Package 1 Width	0.16 in (0.400 cm)	
Package 1 Length	0.55 in (1.400 cm)	
Package 1 Weight	0.00 oz (0.100 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	1000	
Package 2 Height	0.79 in (2.000 cm)	
Package 2 Width	4.53 in (11.500 cm)	
Package 2 Length	7.28 in (18.500 cm)	
Package 2 Weight	2.08 oz (59.000 g)	
Unit Type Of Package 3	S01	
Number Of Units In Package 3	25000	
Package 3 Height	5.91 in (15.000 cm)	
Package 3 Width	5.91 in (15.000 cm)	
Package 3 Length	15.75 in (40.000 cm)	
Package 3 Weight	3.66 lb(US) (1.659 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
Ø	Toxic Heavy Metal Free
Ø	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free
②	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	No need of specific recycling operations	