

Product data sheet

Specifications



Circuit Breaker, PowerLink™, 15A,
1 pole, 277VAC, 14kA, remotely
operated, bolt on mount

ECB14015G3

Product availability: Stock - Normally stocked in distribution facility

Price*: 237.00 USD

Main

Product	Circuit breaker
Range Of Product	Powerlink
Circuit Breaker Type	ECB-G3
Circuit Breaker Application	HACR rated HID rated Switching Duty rated
Options	Motor for circuit-breaker 24 V DC
Trip Unit Technology	Thermal-magnetic, standard, LI

Complementary

Line Rated Current	15 A
Product Certifications	UL Listed CSA
Voltage Rating	480Y/277 V AC
Mounting Mode	Bolt-on
Number Of Poles	1P
Interrupt Rating	14 kA 277 V AC 65 kA 120 V AC
Number Of Spaces Required	1
Electrical Connection	Bolted connection
Wire Gauge	AWG 10...AWG 8 aluminium AWG 12...AWG 8 copper

Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	US1DE8A09663
Discount Schedule	DE8A
Gtin	785901335849
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	6.30 in (16.002 cm)
Package 1 Length	9.40 in (23.876 cm)
Package 1 Weight	22.08 oz (625.958 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov