





Transformer, dry type, DOE 2016, 37.5kVA, 1 phase, 240x480V primary, 120/240V secondary, 18H, 150C rise

EE37S3H

Product availability: Stock - Normally stocked in distribution facility

Price*: 8,531.00 USD

Main

Product	Energy Efficient Transformer	
Enclosure Code	18H	
Enclosure Type	NEMA 2	
Insulation Temperature	428 °F (220 °C)	
Phase	1 phase	
Primary Voltage	240 x 480 V	
Power Rating	37.5 kVA	
Secondary Voltage	120/240 V	
Full Capacity Taps	6 2.5 % 2+ 4-	
Temperature Rise	150 °C	
Winding Material	Aluminium	

Complementary

Height	37 in (939.80 mm)
Width	20 in (508.00 mm)
Depth	20 in (508.00 mm)
Net Weight	340.00 lb(US) (154.221 kg)

Ordering and shipping details

Category	US1PE2E16284
Discount Schedule	PE2E
Gtin	785901559016
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43.10 in (100.7 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	21.69 in (55.1 cm)
Package 1 Length	21.50 in (54.6 cm)
Package 1 Weight	376.06 lb(US) (170.579 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov