

Product data sheet

Specifications



Shaft extension, TeSys GS, front, 30A, 320mm

GS1AE7

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 41.85 USD

Main

| | |
|------------------------------------|-------------------|
| Range | TeSys |
| Product Or Component Type | Shaft extension |
| Device Short Name | GS1AE |
| Accessory / Separate Part Category | Locking accessory |
| Product Compatibility | GS |

Complementary

| | |
|--------------------------|-----------------------|
| Switch Rated Current | 30 A |
| Type Of Operating Handle | External |
| Mounting Location | Front |
| Length | 12.60 in (320 mm) |
| Shaft Cross Section | 5 x 5 mm |
| Net Weight | 0.37 lb(US) (0.17 kg) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10I1122640 |
| Discount Schedule | 0I11 |
| Gtin | 3389110181470 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| | |
|------------------------------|--------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.10 in (2.8 cm) |
| Package 1 Width | 1.57 in (4.0 cm) |
| Package 1 Length | 12.60 in (32.0 cm) |
| Package 1 Weight | 4.30 oz (122.0 g) |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 46 |
| Package 2 Height | 11.81 in (30.0 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|-------------------------|
| Package 2 Width | 11.81 in (30.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 13.94 lb(US) (6.325 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|---------------------------|--|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov |