# **Product data sheet**

Specifications



Extended rotary handle, TeSys GV7, yellow legend plate, padlockable, IP55

GV7AP02

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 102.00 USD

#### Main

Range	TeSys	
Product Or Component Type	Extended rotary handle	
Device Short Name	GV7AP	
Range Compatibility	TeSys TeSys GV7 motor circuit breaker TeSys TeSys GV5 motor circuit breaker	
Accessory / Separate Part Category	Control accessory	
Rotary Handle Mounting Location	Front	
Rotary Handle Mounting Style	Extended	

## Complementary

Handle Colour	Red
Handle Front Plate Colour	Yellow
Back/Door Distance	7.2823.62 in (185600 mm)
Rotary Handle Padlocking	1 to 3 padlocks 0.20…0.31 in (5…8 mm) Padlock in OFF position
Net Weight	1.71 lb(US) (0.775 kg)

### Environment

Ip Degree Of Protection

### Ordering and shipping details

IP55

Category	US10I1122366	
Discount Schedule	0l11	
Gtin	3389110567342	
Returnability	Yes	
Country Of Origin	FR	

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.94 in (10 cm)
Package 1 Width	4.13 in (10.5 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length	19.41 in (49.3 cm)
Package 1 Weight	25.64 oz (727 g)
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	11.81 in (30 cm)
Package 2 Width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 2 Weight	11.57 lb(US) (5.25 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	12
Package 3 Height	19.69 in (50 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	37.97 lb(US) (17.224 kg)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes


### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

# Product data sheet

**Dimensions Drawings** 

#### Extended Rotary Handle GV7AP01, GV7AP02



I: 185 minimum, 600 maximum

The shaft of the extended rotary handle GV7AP01 or GV7AP02 must be cut to length: I – 126 mm.