





Safety switch, heavy duty, fusible, 400A, 2 pole, 125HP, 240VAC, 250VDC, neutral factory installed, NEMA1

H225N

Product availability: Stock - Normally stocked in distribution facility

Price*: 3,092.00 USD

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	Neutral (factory installed)	
Phase	3 phase	
Number Of Poles	2	
Current Rating	400 A	
Voltage Rating	250 V DC 240 V AC	
Enclosure Rating	NEMA 1 steel	
Motor Power Hp	50 hp at 240 V AC 50-60 Hz for 3 phase motors 125 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 250 V DC	

Complementary

Short-Circuit Current	10 kA for H or K 200 kA for R or J
Fuse Type	H or K R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 1/0750 kcmil copper or aluminium
Tightening Torque	550 lbf.in (62.14 N.m) (AWG 1/0750 kcmil)
Depth	10.13 in (257.30 mm)
Width	27.63 in (701.80 mm)
Height	50.25 in (1276.35 mm)
Net Weight	175.05 lb(US) (79.4 kg)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100053
Discount Schedule	0DE1
Gtin	785901450429
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.02 in (35.6 cm)
Package 1 Width	27.99 in (71.1 cm)
Package 1 Length	52.01 in (132.1 cm)
Package 1 Weight	175.00 lb(US) (79.379 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov