





Safety switch, heavy duty, fusible, 400A, 4 wire, 3 pole, 1 neutral, 125HP, 240VAC, 250VDC, NEMA 4, 4X, 5, 304 SS

H325NDS

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 15,321.00 USD

Main

| - | |
|---------------------------|--|
| Product | Single Throw Safety Switch |
| Duty Rating | Heavy duty |
| Device Application | Heavy application |
| Disconnect Type | Fusible disconnect |
| Factory Installed Neutral | Neutral (factory installed) |
| Phase | 3 phase |
| Number Of Poles | 3 |
| Current Rating | 400 A |
| Voltage Rating | 250 V DC |
| | 240 V AC |
| Enclosure Rating | NEMA 4/4X/5 stainless steel 304 |
| Motor Power Hp | 50 hp at 240 V AC 50-60 Hz for 3 phase motors 125 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 250 V DC |

Complementary

| Short-Circuit Current | 10 kA for H or K 200 kA for R or J |
|-----------------------|---|
| Fuse Type | H or K R or J |
| Mounting Type | Surface |
| Electrical Connection | Lugs |
| Wiring Configuration | 4-wire (3PH + G) |
| Wire Size | AWG 1/0750 kcmil copper or aluminium |
| Tightening Torque | 550 lbf.in (62.14 N.m) (AWG 1/0750 kcmil) |
| Depth | 10.13 in (257.30 mm) |
| Width | 26.25 in (666.75 mm) |
| Height | 46.25 in (1174.75 mm) |
| Net Weight | 184.97 lb(US) (83.9 kg) |

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

| Category | US10DE100055 |
|-------------------|--------------|
| Discount Schedule | 0DE1 |
| Gtin | 785901195931 |
| Returnability | Yes |
| Country Of Origin | MX |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 18.21 in (46.251 cm) |
| Package 1 Width | 3.99 in (10.13 cm) |
| Package 1 Length | 10.34 in (26.251 cm) |
| Package 1 Weight | 185.00 lb(US) (83.915 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free |
|----------|------------------------------------|
| Ø | Rohs Exemption Information Yes |
| Ø | Pvc Free |
| ② | Halogen Free Plastic Parts Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |