





Mini circuit breaker, Homeline, 20A, 1 pole, 120VAC, 10kA AIR, combo arc fault, plug on neutral, plug in, UL

HOM120PCAFI

Product availability: Stock - Normally stocked in distribution facility

Price*: 267.00 USD

Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	20 A	
Certifications	UL Listed	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	1	
Circuit Breaker Type	Combination ARC-fault	
Ratings	HACR rated	
Electrical Connection	Clamp terminal for 2 cables	
Wire Size	1 x AWG 14AWG 8 (aluminium/copper)	

Complementary

Connections - Terminals	Plug-on neutral	
Tightening Torque 35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)		
Height	3.13 in (79.50 mm)	
Width	1 in (25.40 mm)	
Depth	2.98 in (75.69 mm)	

Environment

Ambient Air Temperature For $$104\ ^{\circ}\text{F}\ (40\ ^{\circ}\text{C})$$ Operation

Ordering and shipping details

Category	US1DE3D06301	
Discount Schedule	DE3D	
Gtin	785901594475	
Returnability	Yes	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin MX

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	4.00 in (10.16 cm)	
Package 1 Width	1.40 in (3.556 cm)	
Package 1 Length	5.10 in (12.954 cm)	
Package 1 Weight	9.76 oz (276.691 g)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	2160	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	42.00 in (106.68 cm)	
Package 2 Length	42.00 in (106.68 cm)	
Package 2 Weight	1373.00 lb(US) (622.782 kg)	
Unit Type Of Package 3	CAR	
Number Of Units In Package 3	40	
Package 3 Height	3.70 in (9.398 cm)	
Package 3 Width	13.60 in (34.544 cm)	
Package 3 Length	20.80 in (52.832 cm)	
Package 3 Weight	24.75 lb(US) (11.226 kg)	

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Halogen Free Product	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information