





Mini branch circuit breaker, Homeline, 150A, 4 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM2150BB

Product availability: Stock - Normally stocked in distribution facility

Price*: 428.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	150 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	4P
Short Circuit Current Rating	10 kA
Number Of Spaces	4
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 4300 kcmil (aluminium/copper)

Complementary

Tightening Torque	250.48 lbf.in (28.3 N.m) 0.150.23 in² (95150 mm²) (AWG 4/0250 kcmil)
Height	5.39 in (136.91 mm)
Width	3.98 in (101.09 mm)
Depth	3.13 in (79.50 mm)

Environment

Ambient Air Temperature For	104 °F (40 °C)
Operation	, ,

Ordering and shipping details

Category	US1DE3D00144
Discount Schedule	DE3D
Gtin	785901296201
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.80 in (14.732 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	3.07 lb(US) (1.393 kg)

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov