# Product data sheet

Specifications



SQUARE D



Load center, Homeline, 1 phase, 30 spaces, 60 circuits, 225A convertible main lugs, PoN, NEMA1, gnd bar, combo cover

HOM3060L225PGC

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 517.32 USD

### Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	PoN Convertible Mains (lugs)
Rated Current	225 A
Number Of Spaces	30
Maximum Number Of Single Pole Circuits	60
Enclosure Rating	NEMA 1 indoor
Cover Type	Combination flush/surface cover
Electrical Connection	Lugs
Provided Equipment	Grounding bar 1)

## Complementary

10 kA
30
1 phase
120/240 V AC
AWG 4250 kcmil copper AWG 4300 kcmil aluminium
Grounding bar included (not installed)
3-wire
Tin plated aluminium: busbar
Welded sheet steel
Baked enamel Gray
10
225.0 A
33.78 in (858 mm)
14.25 in (362 mm)
3.74 in (95 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## Environment

Ambient Air Temperature For	23 °F (-5 °C)
Operation	104 °F (40 °C)
Product Certifications	UL listed file E-6294

## Ordering and shipping details

Category	US1DE3C00045
Discount Schedule	DE3C
Gtin	785901977223
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.50 in (13.97 cm)
Package 1 Width	16.30 in (41.402 cm)
Package 1 Length	36.40 in (92.456 cm)
Package 1 Weight	30.64 lb(US) (13.9 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	18
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	576.52 lb(US) (261.504 kg)

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov