



TeSys Deca - auxiliary contact - 3 NO early-break

GV3A05

! Discontinued on: Jan 23, 2021

! Discontinued

Main

Range	TeSys
Device Short Name	GV3A
Product Or Component Type	Auxiliary contact block
Product Compatibility	GV3ME
Mounting Location	Right side
Pole Contact Composition	3 NO
Quantity Per Set	Set of 10

Complementary

•	
[Ui] Rated Insulation Voltage	600 V UL 508 690 V IEC 60947-1
	600 V CSA C22.2 No 14
	600 V CSA C22.2 NO 14
[Ue] Rated Operational Voltage	48690 V AC
	24220 V DC
[Ith] Conventional Free Air Thermal Current	6 A
Mechanical Durability	100000 cycles
Protection Type	GB2CB circuit breaker
	GG fuse 6 A
Rated Operational Power In Va	350 VA 48 V AC-11 100000 cycles
	700 VA 440 V AC-11 100000 cycles
	700 VA 500 V AC-11 100000 cycles
	400 VA 690 V AC-11 100000 cycles
	500 VA 110127 V AC-11 100000 cycles
	800 VA 220240 V AC-11 100000 cycles
	850 VA 380415 V AC-11 100000 cycles
Rated Operational Power In W	180 W 24 V DC-11 100000 cycles
	240 W 48 V DC-11 100000 cycles
	180 W 60 V DC-11 100000 cycles
	140 W 110 V DC-11 100000 cycles
	120 W 220 V DC-11 100000 cycles
Net Weight	0.15 lb(US) (0.07 kg)

Environment

Environmental Characteristic Normal environment

Ordering and shipping details

Category	22366-MAN STR PROTECTORS-GV1/GV3
Discount Schedule	l11

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3389110343397	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	3.15 in (8 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	1.59 oz (45 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov