

# Product data sheet

Specifications



Quad tandem circuit breaker,  
Homeline, 1 x 2 pole at 30A, 1 x 2  
pole at 40A, 120/240VAC, 10kA  
AIR, plug in, UL

HOMT230240

Product availability: Stock - Normally stocked in distribution facility

Price\*: 130.00 USD

## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A 40 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2.0
Circuit Breaker Type	Quad tandem
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 14...AWG 8 ( aluminium/copper ) 1 x AWG 14...AWG 6 ( aluminium/copper )

## Complementary

Tightening Torque	35.40...40.71 lbf.in (4.0...4.6 N.m) 0.00...0.02 in² (2.5...10 mm²) (AWG 14...AWG 6) 35.40...40.71 lbf.in (4.0...4.6 N.m) 0.00...0.03 in² (2.5...20 mm²) (AWG 12...AWG 6)
Height	3.13 in (79.50 mm)
Width	1.97 in (50.04 mm)
Depth	3.29 in (83.57 mm)

## Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901041009
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.03 in (7.7 cm)
Package 1 Width	3.11 in (7.9 cm)
Package 1 Length	3.31 in (8.4 cm)
Package 1 Weight	13.62 oz (386 g)

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)