# Product data sheet

Specifications



## Safety switch, heavy duty, fusible, 400A, 4 wire, 3 pole, 1 neutral, 125hp, 240VAC/250VDC, NEMA 1

H325N

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 3,788.00 USD

### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Phase	3 phase
Number Of Poles	3
Current Rating	400 A
Voltage Rating	250 V DC 240 V AC
Enclosure Rating	NEMA 1 steel
Motor Power Hp	50 hp at 240 V AC 50-60 Hz for 3 phase motors 125 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 250 V DC

### Complementary

•	
Short-Circuit Current	10 kA for H or K 200 kA for R or J
Fuse Туре	H or K R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire (3PH + G)
Wire Size	AWG 1/0750 kcmil copper or aluminium
Tightening Torque	550 lbf.in (62.14 N.m) (AWG 1/0750 kcmil)
Depth	10.13 in (257.30 mm)
Width	27.63 in (701.80 mm)
Height	50.25 in (1276.35 mm)
Net Weight	173.06 lb(US) (78.5 kg)

#### Environment

Certifications

UL listed file E2875

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10DE100053
Discount Schedule	0DE1
Gtin	785901450368
Returnability	Yes
Country Of Origin	MX

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.21 in (36.1 cm)
Package 1 Width	28.19 in (71.6 cm)
Package 1 Length	52.09 in (132.3 cm)
Package 1 Weight	168.00 lb(US) (76.203 kg)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

## Certifications & Standards

REACh Declaration
Compliant with Exemptions
China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov