





Safety switch, heavy duty, fusible, 60A, 3 wire, 3 pole, 50HP, 600V AC/DC, NEMA 4, 4X, 5, 304 stainless steel

H362DS



Discontinued on: Jun 23, 2023

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	60 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 4/4X/5 stainless steel 304	
Motor Power Hp	15 hp at 480 V AC 50-60 Hz for 3 phase motors 30 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 3 phase motors 30 hp at 600 V DC	

### Complementary

Short-Circuit Current	10 kA for H or K
	200 kA for R or J
Fuse Type	H or K
	R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 14AWG 3 copper
	AWG 12AWG 3 aluminium
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 3)
	45 lbf.in (5.08 N.m) (AWG 6AWG 4)
	40 lbf.in (4.52 N.m) 0.01 in <sup>2</sup> (8.367 mm <sup>2</sup> ) (AWG 8)
	50 lbf.in (5.65 N.m) 0.000.01 in <sup>2</sup> (2.065.261 mm <sup>2</sup> ) (AWG 14AWG 10)
Depth	6.97 in (177.04 mm)
Width	10.81 in (274.57 mm)
Height	16.87 in (428.50 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Net Weight 22.05 lb(US) (10 kg)

#### **Environment**

Certifications UL listed file E2875

# Ordering and shipping details

Category	US10DE100010
Discount Schedule	0DE1
Gtin	785901023661
Returnability	Yes
Country Of Origin	IIS

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.70 in (22.098 cm)
Package 1 Width	13.30 in (33.782 cm)
Package 1 Length	20.70 in (52.578 cm)
Package 1 Weight	18.95 lb(US) (8.596 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	40
Package 2 Height	43.50 in (110.49 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	788.00 lb(US) (357.43 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov