





Safety switch, heavy duty, non fusible, 60A, 3 pole, 60hp, 600VAC/DC, NEMA 12K

HU362A

! Discontinued on: Jan 31, 2024



Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number Of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 12K galvannealed steel
Motor Power Hp	10 hp at 240 V AC 50-60 Hz for 1 phase motors 20 hp at 240 V AC 50-60 Hz for 3 phase motors 25 hp at 480 V AC 50-60 Hz for 1 phase motors 50 hp at 480 V AC 50-60 Hz for 3 phase motors 30 hp at 600 V AC 50-60 Hz for 1 phase motors 60 hp at 600 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC 30 hp at 600 V DC

## Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 14AWG 3 copper AWG 12AWG 3 aluminium
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 3) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 50 lbf.in (5.65 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)
Depth	7 in (177.80 mm)
Width	10.5 in (266.70 mm)
Height	16.5 in (419.10 mm)
Net Weight	17.64 lb(US) (8 kg)

### **Environment**

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

# Ordering and shipping details

Category	US10DE100114
Discount Schedule	0DE1
Gtin	785901505051
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.40 in (18.796 cm)
Package 1 Width	10.90 in (27.686 cm)
Package 1 Length	20.00 in (50.8 cm)
Package 1 Weight	16.86 lb(US) (7.648 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov