





Safety switch, heavy duty, non fusible, 60A, 600VAC/DC, 3 poles, 60HP, NEMA 12K, Crouse-Hinds Arktite

HU362AWC

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,678.00 USD

Main

Product	Receptacle Switch	
For Use With	Plug APJ6485 Crouse-Hinds Arktite	
Disconnect Type	Non-fusible disconnect switch	
Phase	3 phase	
Number Of Poles	3	
Current Rating	60 A	
Voltage Rating	600 V AC 250 V DC	
Enclosure Rating Nema 3R	NEMA 12K	
Maximum Horse Power Rating	50 hp at 480 V AC 50-60 Hz for 3 phase motors 60 hp at 600 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC	

Complementary

Mounting Type	Surface	
Electrical Connection	Receptacle	
Wire Configuration	4-wire	
Wire Size	AWG 12AWG 2 aluminium AWG 14AWG 2 copper	
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) (AWG 8) 35 lbf.in (3.95 N.m) (AWG 14AWG 10)	
Depth	7 in (177.80 mm)	
Width	10.5 in (266.70 mm)	
Height	16.5 in (419.10 mm)	

Environment

Certifications UL Listed

Ordering and shipping details

Category	US10DE100118	
Discount Schedule	0DE1	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	785901195634	
Returnability	Yes	
Country Of Origin	IIS	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.40 in (23.876 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	27.70 in (70.358 cm)
Package 1 Weight	24.03 lb(US) (10.9 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov