



Safety switch, heavy duty, non fusible, 200A, 3 poles, 150hp, 600VAC/DC, neutral factory installed, NEMA1

HU364N

! Discontinued on: Jan 31, 2024

Product availability: Stock - Normally stocked in distribution

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Non-fusible disconnect	
Factory Installed Neutral	Neutral (factory installed)	
Phase	3 phase	
Number Of Poles	3	
Current Rating	200 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 1 steel	
Motor Power Hp	15 hp at 240 V AC 50-60 Hz for 1 phase motors 60 hp at 240 V AC 50-60 Hz for 3 phase motors 50 hp at 480 V AC 50-60 Hz for 1 phase motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 1 phase motors 50 hp at 600 V AC 50-60 Hz for 1 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC	

Complementary

Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	4-wire (3PH + N)	
Wire Size	AWG 6250 kcmil copper or aluminium	
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)	
Depth	8.25 in (209.55 mm)	
Width	18.5 in (469.90 mm)	
Height	29 in (736.60 mm)	
Net Weight	42.99 lb(US) (19.5 kg)	

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100008
Discount Schedule	0DE1
Gtin	785901078050
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.20 in (20.828 cm)
Package 1 Width	19.30 in (49.022 cm)
Package 1 Length	30.70 in (77.978 cm)
Package 1 Weight	42.90 lb(US) (19.459 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov